



JBL MicroMec CristalProfi e

High-performance filter balls for CristalProfi e

Suitable for:     



- Clean and healthy water: high-performance filter balls with highly porous structure for CristalProfi e
- To use: Transfer into the filter basket. Rinse with water, insert into the filter.
- Outer layer: breakdown of ammonium and nitrite, bacteria on the inside: breakdown of nitrate.
- Biological filter material made of sintered glass: helps beneficial cleansing bacteria to settle more quickly
- Package contents: 1 x high-performance filter balls 1 l.




JBL MicroMec CristalProfi e



Product information

Clean and healthy water

Plant and food remains and metabolic substances lead to a deterioration of the quality of the water in the aquarium. Good water quality is necessary for healthy fish and plants. This can be achieved with various filters and filter materials. The filters suck in the aquarium water and remove the pollution and waste materials with the filter material from the water.

| Further information | |
|-----------------------|---|
| FAQ | ✓ |
| Blog | ✓ |
| Press | ✓ |
| Laboratory/calculator | ✗ |
| Worth reading | ✓ |
| Spare parts | ✗ |
| Video | ✓ |
| GarantiePlus | ✗ |
| Instructions | ✓ |
| QR code |  |





JBL MicroMec CristalProfi e



Product details

| Article data | | |
|--------------------------|--|--|
| Product name | JBL MicroMec CristalProfi e4/7/900/1,2 | JBL MicroMec CristalProfi e15/1900/1,2 |
| Art. No. | 6017700 | 6017800 |
| EAN number | 4014162601773 | 4014162601780 |
| EAN as barcode | | |
| Content | 1000 ml | 1600 ml |
| For CPe | 4-7-901,2 | 15-1901,2 |
| Expiry months | - | - |
| RRP incl. VAT | - | - |
| Base price | - | - |
| Nominal filling quantity | - | - |
| Base quantity | 1 | 1 |
| Gross weight | 744 g | 1211 g |
| Net weight | 655 g | 1109 g |
| Weight change | 1000 | 1000 |

| Disposal | | |
|-------------------------|--|--|
| Product name | JBL MicroMec CristalProfi e4/7/900/1,2 | JBL MicroMec CristalProfi e15/1900/1,2 |
| Art. No. | 6017700 | 6017800 |
| Green dot | ✓ | ✓ |
| Group electronic waste | - | - |
| Disposal weight | - | - |
| Battery type | - | - |
| Battery return | - | - |
| Battery rechargeable | - | - |
| Disposal weight battery | - | - |
| Non-returnable glass | - | - |
| PPK | 86 g | 102 g |
| Plastic small | 2 g | 2 g |
| Plastic large | - | - |
| Disposal weight metal | 0 g | 0 g |

| Features | | |
|--------------|--|--|
| Product name | JBL MicroMec CristalProfi e4/7/900/1,2 | JBL MicroMec CristalProfi e15/1900/1,2 |
| Art. No. | 6017700 | 6017800 |





| Features | | |
|----------------------|--|--|
| Animal species | Arowana, Axolotl, Barbels, Bettas, Bichirs/reedfish, Blowfish, Catfish, Cichlids (South America), Corals, Crayfish, Danions, Discus, Dwarf shrimps, Flowerhorn, Gobies, Goldfish, Gouramis, Guppy, Juvenile fish, Killifish, Livebearers, Loaches, Mussels, Newts, Panchaxes, Rainbowfish, Snails, Spiny eels, Terrapins, Tetra, Tropical terrapins, Veiltails, freshwater butterflyfish, turtle | Arowana, Axolotl, Barbels, Bettas, Bichirs/reedfish, Blowfish, Catfish, Cichlids (South America), Corals, Crayfish, Danions, Discus, Dwarf shrimps, Flowerhorn, Gobies, Goldfish, Gouramis, Guppy, Juvenile fish, Killifish, Livebearers, Loaches, Mussels, Newts, Panchaxes, Rainbowfish, Snails, Spiny eels, Terrapins, Tetra, Tropical terrapins, Veiltails, freshwater butterflyfish, turtle |
| Animal size | For all animal sizes | For all animal sizes |
| Animal age group | All aquarium fish | All aquarium fish |
| Volume of habitat | > 300 L | 800 L |
| Material | sintered glass | sintered glass |
| Food type | - | - |
| Colour | white | white |
| Dosage | - | - |
| Transport conditions | - | - |



JBL MicroMec CristalProfi e

| Electronic label / illuminant | | |
|-------------------------------|--|--|
| Product name | JBL MicroMec CristalProfi e4/7/900/1,2 | JBL MicroMec CristalProfi e15/1900/1,2 |
| Art. No. | 6017700 | 6017800 |
| Ambient temperature | - | - |
| Start time | - | - |
| Mercury | - | - |
| Tube length | - | - |
| Service life | - | - |
| Lumen | - | - |
| CRI value | - | - |
| Dimmable | - | - |
| Switching cycles | - | - |
| PAR value | - | - |
| Energy efficiency class | - | - |
| UV-A | - | - |
| UV-B | - | - |
| UV-C | - | - |
| Colour temperature | - | - |
| Base designation | - | - |

| Technical data | | |
|-------------------------------|--|--|
| Product name | JBL MicroMec CristalProfi e4/7/900/1,2 | JBL MicroMec CristalProfi e15/1900/1,2 |
| Art. No. | 6017700 | 6017800 |
| Range in litres | - | - |
| Range from - to | - | - |
| Range in days | - | - |
| Range tank length | - | - |
| Output in watts | - | - |
| Output per hour | - | - |
| Output per day | - | - |
| Height | - | - |
| Length | - | - |
| Width | - | - |
| Diameter | - | - |
| Voltage | - | - |
| For | - | - |
| T8 26mm (watt) | - | - |
| T5 16mm (watt) | - | - |
| Size | - | - |
| Content for | - | - |
| Filter container volume | - | - |
| Volume filter media | - | - |
| Hose connections pressure/out | - | - |
| Hose connections suction/in | - | - |





| Technical data | | |
|----------------|---|---|
| Delivery head | - | - |





JBL MicroMec CristalProfi e

| | |
|------------------|---|
| Food type | - |
| Sub product type | - |
| Dosing | - |





Additional information for the specialist trade sector

| Article data | | |
|----------------------|--|--|
| Product name | JBL MicroMec CristalProfi e4/7/900/1,2 | JBL MicroMec CristalProfi e15/1900/1,2 |
| Art. No. | 6017700 | 6017800 |
| VAT | 20% | 20% |
| Sales unit (SU) | 3 | 3 |
| Volume packaging | 1.98l | 2.4l |
| Dimensions (l/w/h) | 70 mm/160 mm/177 mm | 70 mm/175 mm/196 mm |
| Layer | 48 | 54 |
| Pallet | 240 | 216 |
| Category of products | 2 | 2 |
| Customs tariff | 70200080 | 70200080 |
| Country of origin | CN | CN |
| Type of packaging | Faltschachtel/Karton | Faltschachtel/Karton |

| PU 1 data | | |
|------------------|--|--|
| Product name | JBL MicroMec CristalProfi e4/7/900/1,2 | JBL MicroMec CristalProfi e15/1900/1,2 |
| Art. No. | 6017700 | 6017800 |
| PU 1 material | film gr | film gr |
| PU 1 weight | 3.7 g | 3.8 g |
| PU 1 length | 160 mm | 175 mm |
| PU 1 width/depth | 200 mm | 220 mm |
| PU 1 height | 180 mm | 200 mm |

| PU 2 data | | |
|------------------|--|--|
| Product name | JBL MicroMec CristalProfi e4/7/900/1,2 | JBL MicroMec CristalProfi e15/1900/1,2 |
| Art. No. | 6017700 | 6017800 |
| PU 2 material | cardboard gr | cardboard gr |
| PU 2 weight | 650 g | 720 g |
| PU 2 length | 400 mm | 400 mm |
| PU 2 width/depth | 420 mm | 420 mm |
| PU 2 height | 340 mm | 370 mm |

| Trade data | | |
|-------------------|--|--|
| Product name | JBL MicroMec CristalProfi e4/7/900/1,2 | JBL MicroMec CristalProfi e15/1900/1,2 |
| Art. No. | 6017700 | 6017800 |
| Till receipt text | MicroMec e7/e9 | MicroMec e1500 |
| Shelf placement | - | - |