



# JBL CRISTALPROFI CLEARMEC e

Nitrite, nitrate, phosphate remover for CristalProfi e

Suitable for:



- Clean and healthy water: set with nitrite, nitrate and phosphate removers for CristalProfi e filter baskets
- To use: remove the plastic bag, put the complete set into the empty filter basket (penultimate seen from above), put the filter basket back into the filter
- Removes toxic nitrogen compound nitrite (NO<sub>2</sub>), algae promoting nitrogen compound nitrate (NO<sub>3</sub>) and algae promoting phosphate (PO<sub>4</sub>)
- Mix of clay balls and special resin in filter bag, centrally located in the foam cut-out. Thus only a part of the water flows through the bag and the slow flow increases the effect. Main water flow passes through the foam
- Package contents: 1 set with a bag of nitrite, nitrate and phosphate removers and 2 foam inserts on top of each other with rounded cut-out for filter bag

You may also be interested in

You can find a complete overview here: <https://www.jbl.de/qr/60175>



**JBL Symec micro**  
 Microfibre fleece against water cloudiness



**JBL Symec Filter floss**  
 Filter wool to remove all types of cloudiness



**JBL Symec XL**  
 Coarse filter wool to remove all types of water cloudiness



**JBL Symec VL**  
 Filter wool fleece to remove water cloudiness





# JBL CRISTALPROFI CLEARMEC e




## Product information

### Clean and healthy water

Plant and food remains and metabolic substances lead to a deterioration in the quality of the water in the aquarium. Good water quality is necessary for healthy fish and plants. This can be achieved with various filters and filter materials. The filters suck in the aquarium water and remove the pollution and waste materials with the filter material from the water.

This set consists of round foam inserts for the JBL CristalProfi e filter baskets, which have a bag of dedicated filter material at their core. This means that the main water flow in the filter goes through the foam on the outside and a slowed, reduced flow of water goes through the central filter bag. The dedicated filter material thus perfectly binds the troublesome substances nitrite, nitrate and phosphate and removes them from the water. Water tests are the easiest way to determine when the set needs to be replaced.

Nitrite (NO<sub>2</sub>) poisons the blood of aquarium fish and amounts as low as 0.4 mg/l can lead to death. Nitrate (NO<sub>3</sub>) is non-toxic, but a mere 20 mg/l can act as a nutrient to promote the growth of all types of algae (except diatoms). Phosphate (PO<sub>4</sub>) is also non-toxic, but from 0.3 mg/l it starts to promote the growth of all types of algae (except diatoms)

| Further information   |   |
|-----------------------|---|
| FAQ                   | ✓   |
| Blog                  | ✓   |
| Press                 | ✗   |
| Laboratory/calculator | ✗   |
| Worth reading         | ✓   |
| Spare parts           | ✗   |
| Video                 | ✓   |
| GarantiePlus          | ✗   |
| Instructions          | ✓   |
| QR code               |  |





# JBL CRISTALPROFI CLEARMEC e



## Product details

| Article data             |  |  |
|--------------------------|--|--|
| Product name             | JBL CRISTALPROFI CLEARMEC e4/7/900/1,2 | JBL CRISTALPROFI CLEARMEC e15/1900/1,2 |
| Art. No.                 | 6017500                                | 6017600                                |
| EAN number               | 4014162601759                          | 4014162601766                          |
| EAN as barcode           |  |  |
| Content                  | 500 ml                                 | 800 ml                                 |
| For CPe                  | 4-7-901,2                              | 15-1901,2                              |
| Expiry months            | -                                      | -                                      |
| RRP incl. VAT            | 17,22 €                                | 23,42 €                                |
| Base price               | 34,44 €                                | -                                      |
| Nominal filling quantity | 500 ml                                 | -                                      |
| Base quantity            | 1 l                                    | 1                                      |
| Gross weight             | 476 g                                  | 697 g                                  |
| Net weight               | 388 g                                  | 593 g                                  |
| Weight change            | 1000                                   | 1000                                   |

| Disposal                |  |  |
|-------------------------|--|--|
| Product name            | JBL CRISTALPROFI CLEARMEC e4/7/900/1,2 | JBL CRISTALPROFI CLEARMEC e15/1900/1,2 |
| Art. No.                | 6017500                                | 6017600                                |
| Green dot               | ✓                                      | ✓                                      |
| Group electronic waste  | -                                      | -                                      |
| Disposal weight         | -                                      | -                                      |
| Battery type            | -                                      | -                                      |
| Battery return          | -                                      | -                                      |
| Battery rechargeable    | -                                      | -                                      |
| Disposal weight battery | -                                      | -                                      |
| Non-returnable glass    | -                                      | -                                      |
| PPK                     | 73 g                                   | 102 g                                  |
| Plastic small           | 15 g                                   | 2 g                                    |
| Plastic large           | -                                      | -                                      |
| Disposal weight metal   | 0 g                                    | 0 g                                    |

| Features     |  |  |
|--------------|--|--|
| Product name | JBL CRISTALPROFI CLEARMEC e4/7/900/1,2 | JBL CRISTALPROFI CLEARMEC e15/1900/1,2 |
| Art. No.     | 6017500                                | 6017600                                |





| Features             |   |   |
|----------------------|---|---|
| Animal species       | Armored catfish, Arowana, Axolotl, Barbels, Bettas, Bichirs/ reedfish, Blowfish, Catfish, Cichlids (South America), Clawed frogs, Clawed shrimps, Crayfish, Crustaceans, Danions, Discus, Dwarf crayfish, Dwarf shrimps, Flowerhorn, Gill maggots, Goldfish, Gouramis, Guppy, Juvenile fish, Killifish, Livebearers, Loaches, Mussels, Newts, Panchaxes, Rainbowfish, Snails, Spiny eels, Tetra, Tropical terrapins, Veiltails, blood parrot cichlids, freshwater butterflyfish, turtle | Armored catfish, Arowana, Axolotl, Barbels, Bettas, Bichirs/ reedfish, Blowfish, Catfish, Cichlids (South America), Clawed frogs, Clawed shrimps, Crayfish, Crustaceans, Danions, Discus, Dwarf crayfish, Dwarf shrimps, Flowerhorn, Gill maggots, Goldfish, Gouramis, Guppy, Juvenile fish, Killifish, Livebearers, Loaches, Mussels, Newts, Panchaxes, Rainbowfish, Snails, Spiny eels, Tetra, Tropical terrapins, Veiltails, blood parrot cichlids, freshwater butterflyfish, turtle |
| Animal size          | For all animal sizes  | For all animal sizes  |
| Animal age group     | All aquarium fish   | All aquarium fish   |
| Volume of habitat    | > 300 L   | 800 L   |
| Material             | -   | -   |
| Food type            | -   | -   |
| Colour               | blue  | blue  |
| Dosage               | -   | -   |
| Transport conditions | -   | -   |



# JBL CRISTALPROFI CLEARMEC e

| Electronic label / illuminant |  |  |
|-------------------------------|--|--|
| Product name                  | JBL CRISTALPROFI CLEARMEC e4/7/900/1,2 | JBL CRISTALPROFI CLEARMEC e15/1900/1,2 |
| Art. No.                      | 6017500                                | 6017600                                |
| Ambient temperature           | -                                      | -                                      |
| Start time                    | -                                      | -                                      |
| Mercury                       | -                                      | -                                      |
| Tube length                   | -                                      | -                                      |
| Service life                  | -                                      | -                                      |
| Lumen                         | -                                      | -                                      |
| CRI value                     | -                                      | -                                      |
| Dimmable                      | -                                      | -                                      |
| Switching cycles              | -                                      | -                                      |
| PAR value                     | -                                      | -                                      |
| Energy efficiency class       | -                                      | -                                      |
| UV-A                          | -                                      | -                                      |
| UV-B                          | -                                      | -                                      |
| UV-C                          | -                                      | -                                      |
| Colour temperature            | -                                      | -                                      |
| Base designation              | -                                      | -                                      |

| Technical data                |  |  |
|-------------------------------|--|--|
| Product name                  | JBL CRISTALPROFI CLEARMEC e4/7/900/1,2 | JBL CRISTALPROFI CLEARMEC e15/1900/1,2 |
| Art. No.                      | 6017500                                | 6017600                                |
| Range in litres               | -                                      | -                                      |
| Range from - to               | -                                      | -                                      |
| Range in days                 | -                                      | -                                      |
| Range tank length             | -                                      | -                                      |
| Output in watts               | -                                      | -                                      |
| Output per hour               | -                                      | -                                      |
| Output per day                | -                                      | -                                      |
| Height                        | -                                      | -                                      |
| Length                        | -                                      | -                                      |
| Width                         | -                                      | -                                      |
| Diameter                      | -                                      | -                                      |
| Voltage                       | -                                      | -                                      |
| For                           | -                                      | -                                      |
| T8 26mm (watt)                | -                                      | -                                      |
| T5 16mm (watt)                | -                                      | -                                      |
| Size                          | -                                      | -                                      |
| Content for                   | -                                      | -                                      |
| Filter container volume       | -                                      | -                                      |
| Volume filter media           | -                                      | -                                      |
| Hose connections pressure/out | -                                      | -                                      |
| Hose connections suction/in   | -                                      | -                                      |





| Technical data |   |   |
|----------------|---|---|
| Delivery head  | - | - |





# JBL CRISTALPROFI CLEARMEC e

|                  |   |
|------------------|---|
| Food type        | - |
| Sub product type | - |
| Dosing           | - |





## Additional information for the specialist trade sector

| Article data         |  |  |
|----------------------|--|--|
| Product name         | JBL CRISTALPROFI CLEARMEC e4/7/900/1,2 | JBL CRISTALPROFI CLEARMEC e15/1900/1,2 |
| Art. No.             | 6017500                                | 6017600                                |
| VAT                  | 19%                                    | 19%                                    |
| Sales unit (SU)      | 3                                      | 3                                      |
| Volume packaging     | 1.98l                                  | 2.4l                                   |
| Dimensions (l/w/h)   | 70 mm/160 mm/177 mm                    | 70 mm/175 mm/196 mm                    |
| Layer                | 120                                    | 72                                     |
| Pallet               | 360                                    | 288                                    |
| Category of products | 2                                      | 2                                      |
| Customs tariff       | 28182000                               | 28182000                               |
| Country of origin    | BE                                     | BE                                     |
| Type of packaging    | Faltschachtel/Karton                   | Faltschachtel/Karton                   |

| PU 1 data        |  |  |
|------------------|--|--|
| Product name     | JBL CRISTALPROFI CLEARMEC e4/7/900/1,2 | JBL CRISTALPROFI CLEARMEC e15/1900/1,2 |
| Art. No.         | 6017500                                | 6017600                                |
| PU 1 material    | film gr                                | film gr                                |
| PU 1 weight      | 3.7 g                                  | 3.8 g                                  |
| PU 1 length      | 160 mm                                 | 175 mm                                 |
| PU 1 width/depth | 200 mm                                 | 220 mm                                 |
| PU 1 height      | 180 mm                                 | 200 mm                                 |

| PU 2 data        |  |  |
|------------------|--|--|
| Product name     | JBL CRISTALPROFI CLEARMEC e4/7/900/1,2 | JBL CRISTALPROFI CLEARMEC e15/1900/1,2 |
| Art. No.         | 6017500                                | 6017600                                |
| PU 2 material    | cardboard gr                           | cardboard gr                           |
| PU 2 weight      | 650 g                                  | 720 g                                  |
| PU 2 length      | 500 mm                                 | 550 mm                                 |
| PU 2 width/depth | 370 mm                                 | 415 mm                                 |
| PU 2 height      | 360 mm                                 | 310 mm                                 |

| Trade data        |  |  |
|-------------------|--|--|
| Product name      | JBL CRISTALPROFI CLEARMEC e4/7/900/1,2 | JBL CRISTALPROFI CLEARMEC e15/1900/1,2 |
| Art. No.          | 6017500                                | 6017600                                |
| Till receipt text | ClearMec+ e7/e9                        | ClearMec+ e1500                        |
| Shelf placement   | -                                      | -                                      |

