

Pre-filter pads and filter foam for CristalProfi e

<image>

- Clean and healthy water: pre-filter pad and filter foam pad for the top basket of the filter CristalProfi e
- Use: insert for the top filter basket
- 1 medium-pored foam pad 20 ppi, 1 fine-pored foam pad 30 ppi
- Freshwater and saltwater neutral, no release of harmful substances
- Package content: 4 pre-filter pads 10 ppi, 1 filter foam 20 ppi, 1 filter foam 30 ppi



You may also be interested in You ca

You can find a complete overview here: https://www.jbl.de/qr/60159





JBL Symec micro Microfibre fleece against water cloudiness



JBL Symec Filter floss Filter wool to remove all types of cloudiness



JBL Symec XL Coarse filter wool to remove all types of water cloudiness



JBL Symec VL Filter wool fleece to remove water cloudiness





Product information

Quality of foam:

Foams used in aquaristics with live animals must always be subjected to a pollutant test, as most plastics release problematic plasticisers into the water. All the plastics used by JBL have passed this test and do NOT release any harmful substances into the water.

Cleaning of plastics:

For many months it is sufficient to rinse the dirty filter sponges under lukewarm running water and then inoculate them with filter bacteria (JBL FilterStart) before using them again. However, as mechanical cleaning NEVER leads to complete cleaning and dirt will remain in the filter sponge, it is recommended you replace the filter sponges about every 6 months. If you place a freshly cleaned filter sponge in a glass of clean water overnight, you will be able to smell how much dirt is still present in the supposedly clean sponge the next morning!

Inoculating filter material with cleansing bacteria:

Initial colonisation of filter material with cleansing bacteria takes about 1-2 weeks in freshwater and twice as long in seawater. If the filter material was already in use, the time for a "recolonisation" is doubled, as recolonisation does not take place so easily on dead bacterial lawns. The addition of concentrated cleansing bacteria such as in JBL FilterStart shortens the biological start-up time to about 24 hours. Another benefit is when you fill the existing settlement space in the filter material with beneficial bacteria, pathogenic germs find no place to spread. This has now been scientifically proven.

Further information	
FAQ	✓ ✓
Blog	✓
Press	×
Laboratory/calculator	×
Worth reading	~
Spare parts	×
Video	✓
GarantiePlus	×
Instructions	~
QR code	





Product details

Article data		
Product name	JBL CristalProfi e4/7/900/1 CombiBloc	JBL CristalProfi e15/1900/1 CombiBloc
Art. No.	6015900	6016000
EAN number	4014162601599	4014162601605
EAN as barcode		
Content	6 pcs.	6 pcs.
For CPe	4-7-901	15-1901
Expiry months	-	-
RRP incl. VAT	14,11 €	21,53€
Base price	-	-
Nominal filling quantity	-	-
Base quantity	1	1
Gross weight	100 g	130 g
Net weight	22 g	30 g
Weight change	1000	1000
Disposal		
Product name	JBL CristalProfi e4/7/900/1 CombiBloc	JBL CristalProfi e15/1900/1 CombiBloc
Art. No.	6015900	6016000
Green dot	✓	\checkmark
Group electronic waste	-	-
Disposal weight	-	-
Battery type	-	-
Battery return	-	-
Battery rechargeable	-	-
Disposal weight battery	-	-
Non-returnable glass	-	-
РРК	78 g	100 g
Plastic small	-	-
Plastic large	-	-
Disposal weight metal	0 g	0 g
Features		
i catures		

Features		
Product name	JBL CristalProfi e4/7/900/1 CombiBloc	JBL CristalProfi e15/1900/1 CombiBloc
Art. No.	6015900	6016000



TECHNICAL PRODUCTS TECHNIK TECHNIQUE

Features		
Animal species	Armored catfish, Arowana, Axoloti, Barbels, Bettas, Bichirs/ reedfish, Blowfish, Catfish, Cichilds (South America), Clawed frogs, Clawed shrimps, Corals, Crayfish, Crustaceans, Danions, Discus, Dwarf crayfish, Dwarf shrimps, Flowerhorn, Gill maggots, Gobies, Goldfish, Gouramis, Guppy, Juvenile fish, Killifish, Livebearers, Loaches, Mussels, Newts, Panchaxes, Rainbowfish, Snails, Spiny eels, Terrapins, Tetra, Tropical terrapins, Tetra, Tropical terrapins, Yeiltails, blood parrot cichilds, freshwater butterflyfish, turtle	Armored catfish, Arowana, Axolotl, Barbels, Bettas, Bichirs/ reedfish, Blowfish, Catfish, Cichlids (South America), Clawed frogs, Clawed shrimps, Corals, Crayfish, Crustaceans, Danions, Discus, Dwarf crayfish, Dwarf shrimps, Flowerhorn, Gill maggots, Gobies, Goldfish, Gouramis, Guppy, Juvenile fish, Killifish, Livebearers, Loaches, Mussels, Newts, Panchaxes, Rainbowfish, Snails, Spiny eels, Terrapins, Tetra, Tropical terrapins, Veiltails, blood parrot cichlids, freshwater butterflyfish, turtle
Animal size	For all animal sizes	For all animal sizes
Animal age group	All aquarium fish	All aquarium fish
Volume of habitat	> 300 L	800 L
Material	polyether	polyether
Food type	-	-
Colour	blue	blue
Dosage	-	-
Transport conditions	-	-





Product name	JBL CristalProfi e4/7/900/1 CombiBloc	JBL CristalProfi e15/1900/ CombiBloc
Art. No.	6015900	6016000
Ambient temperature	-	-
Start time	-	-
Mercury	-	-
Tube length	-	-
Service life	-	-
Lumen	-	-
CRI value	-	-
Dimmable	-	-
Switching cycles	-	-
PAR value	-	-
Energy efficiency class	-	-
UV-A	-	-
UV-B	-	-
UV-C	-	-
Colour temperature	-	-
Base designation	-	-
Product name	JBL CristalProfi e4/7/900/1 CombiBloc	JBL CristalProfi e15/1900/ CombiBloc
Art. No.	6015900	6016000
Range in litres	-	-
Range from - to	-	-
Range in days	-	-
Range tank length		
nunge turnt tengen	-	-
	-	-
Output in watts		
Output in watts Output per hour	-	-
Output in watts Output per hour Output per day	-	-
Output in watts Output per hour Output per day Height	- - -	- - -
Output in watts Output per hour Output per day Height Length	- - - -	- - - - 53 mm
Output in watts Output per hour Output per day Height Length Width	- - - - -	- - - 53 mm 172 mm
Output in watts Output per hour Output per day Height Length Width Diameter	- - - - - - - -	- - - 53 mm 172 mm 123 mm
Output in watts Output per hour Output per day Height Length Width Diameter Voltage		- - - 53 mm 172 mm 123 mm -
Output in watts Output per hour Output per day Height Length Width Diameter Voltage For T8 26mm (watt)		- - - 53 mm 172 mm 123 mm - -
Output in watts Output per hour Output per day Height Length Width Diameter Voltage For		53 mm 172 mm 123 mm
Output in watts Output per hour Output per day Height Length Width Diameter Voltage For T8 26mm (watt)		53 mm 172 mm 123 mm
Output in watts Output per hour Output per day Height Length Width Diameter Voltage For T8 26mm (watt) T5 16mm (watt)		53 mm 172 mm 123 mm



Date: 31.12.2023 Produced by:

Volume filter media

Hose connections pressure/out Hose connections suction/in



Technical data		
Delivery head	-	-





Food type	-
Sub product type	-
Dosing	-





Additional information for the specialist trade sector

Article data		
Product name	JBL CristalProfi e4/7/900/1 CombiBloc	JBL CristalProfi e15/1900/1 CombiBloc
Art. No.	6015900	6016000
VAT	25%	25%
Sales unit (SU)	1	1
Volume packaging	2.031	2.841
Dimensions (l/w/h)	70 mm/165 mm/176 mm	77 mm/180 mm/205 mm
Layer	120	96
Pallet	480	384
Category of products	2	2
Customs tariff	39269097	39269097
Country of origin	CN	CN
Type of packaging	Faltschachtel/Karton	Faltschachtel/Karton

PU 1 data		
Product name	JBL CristalProfi e4/7/900/1 CombiBloc	JBL CristalProfi e15/1900/1 CombiBloc
Art. No.	6015900	6016000
PU 1 material	film gr	film gr
PU 1 weight	3.7 g	3.8 g
PU 1 lengh	480 mm	525 mm
PU 1 width/depth	70 mm	75 mm
PU 1 height	180 mm	205 mm

PU 2 data		
Product name	JBL CristalProfi e4/7/900/1 CombiBloc	JBL CristalProfi e15/1900/1 CombiBloc
Art. No.	6015900	6016000
PU 2 material	cardboard gr	cardboard gr
PU 2 weight	650 g	720 g
PU 2 lengh	500 mm	542 mm
PU 2 width/depth	368 mm	335 mm
PU 2 height	362 mm	430 mm

Trade data		
Product name	JBL CristalProfi e4/7/900/1 CombiBloc	JBL CristalProfi e15/1900/1 CombiBloc
Art. No.	6015900	6016000
Till receipt text	CP e700/e900	CB e1500
Shelf placement	-	-

